

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015291024

Status:

Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid Shunt Terminal Housings, 0.381µm Gold (Au), 2 Circuits, with Open End



Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-7859-001 (PDF)

Packaging Specification PK-70873-0815-001 (PDF)

Test Summary TS-7859-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Accessories
Series	7859
Component Type	Shunt
Overview	C-Grid Connector Products
Product Name	C-Grid, C-Grid III, SL
UPC	800753604384
Physical	
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Resin	Polyester
Net Weight	0.162/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C
Electrical	
Current - Maximum per Contact	5.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	7859-2554N
Reference - Drawing Numbers	
Packaging Specification	PK-70873-0815-001
Product Specification	PS-7859-001
Sales Drawing	SDA-7859-2AXXXN-001
Test Summary	TS-7859-0001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

7859 Series

Use With

70280 C-Grid Breakaway Header, 71308 C-Grid Header, 71764 C-Grid Breakaway Header, 42375 KK Breakaway Header, 42377 KK Breakaway Header, 4030 KK Wire-to-Board Header, 42152 KK Wire-to-Board Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-29-1024](#)