

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192880145

Status:


Active

Overview:

Application Tooling

Description:

ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207126
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200 , 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ETC
Tool Type	Crimp Module
UPC	800753110137
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Material Info	
Engineering Number	ATP-BB-575
Reference - Drawing Numbers	
Application Tooling Documents	ATS-192880145-001, ATS-TOOLING-ID-ATP-001, TM-192280498-001, TM-192280498SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001,

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207126 Series

Use With

Molex Crimp Tape Module 640162000 used with Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex ATP-301 Press: 192280030 and Molex ATP-101 style presses.

Application Tooling Description	FAQ Product #
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Mylar Tape, Tab 2.79 x 0.51mm	190190024
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Mylar Tape, Tab 2.79 x 0.81mm	190190026
Avikrimp Quick Disconnect, Female, for 14-16	190190030

TM-640160065TH-001, TM-640160065TW-001,
TM-640160065VN-001

(2.00-1.30mm²) Wire,
Mylar Tape, Tab 4.75
x 0.51mm
Avikrimp Quick 190190033
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Mylar Tape, Tab 6.35
x 0.81mm
Avikrimp Quick 190190063
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Mylar Tape, Tab 5.21
x 0.81mm
Avikrimp Quick 190190064
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Mylar Tape, Tab 5.21
x 0.51mm
InsulKrimp Quick 190230004
Disconnect,
Male, for 18-22
(0.80-0.35mm²) Wire,
Mylar Tape, Tab 4.75
x 0.51mm
Quixon Quick 192750006
Disconnect, Avikrimp
Style, Female,
Partially Insulated
Blue, 14-16 AWG,
Mylar Tap

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19288-0145](#)