

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [21039-1032](#)
Status: **Active**
Overview: Premo-Flex™ FFC and Etched Polyimide Jumpers
Description: 1.00mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 33 Circuits, 0.051m Cable Length, 0.27mm Cable Thickness, Tin(Sn) Plating
Replacement Part Number: 15267-1032

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-21039-001 \(PDF\)](#)



Series

image - Reference only

General

Product Family	Cable
Series	21039
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	<u>Premo-Flex™ FFC and Etched Polyimide Jumpers</u>
Product Name	Premo-Flex™ FFC Jumper
Replacement Part Number	15267-1032
UPC	756054344651

Physical

Cable Length	0.051m
Circuits (Loaded)	33
Packaging Type	Bag
Pitch - Termination Interface	1.00mm
Temperature Range - Operating	-40°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	1.3A
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers

Product Specification	PS-21039-001
Sales Drawing	SD-21039-002

EU RoHS

ELV and RoHS Compliant
REACH SVHC Not Reviewed
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[21039Series](#)

Use With

www.molex.com/product/ffcfpc_th.html

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[21039-1032](#)