

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395072509

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

3.50mm Pitch Eurostyle Vertical Plug, with Retention Screws, Rear Wire Entry, Gold (Au) Plated, 9 Circuits



|                                |                                                              |
|--------------------------------|--------------------------------------------------------------|
| Documents:                     |                                                              |
| <a href="#">3D Model</a>       | <a href="#">Product Specification PS-39500-001-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |
| <a href="#">3D Model (PDF)</a> |                                                              |

|                               |                           |
|-------------------------------|---------------------------|
| Agency Certification          |                           |
| UL                            | E48521                    |
| General                       |                           |
| Product Family                | Terminal Blocks           |
| Series                        | 39507                     |
| Application                   | N/A                       |
| Comments                      | Rear Wire Entry           |
| Component Type                | Plug                      |
| Overview                      | Eurostyle Terminal Blocks |
| Product Name                  | ESE, Eurostyle Pluggable  |
| Type                          | Euro Block                |
| UPC                           | 822350682695              |
| Physical                      |                           |
| Circuits (Loaded)             | 9                         |
| Entry Angle                   | Horizontal                |
| Lock to Mating Part           | Yes                       |
| Number of Rows                | 1                         |
| Orientation                   | Vertical                  |
| Panel Mount                   | No                        |
| Pitch - Mating Interface      | 3.50mm                    |
| Pitch - Termination Interface | 3.50mm                    |
| Polarized to Mating Part      | Yes                       |
| Stackable                     | No                        |
| Temperature Range - Operating | -40° to +105°C            |
| Wire Size AWG                 | 16, 18, 20, 22, 24        |
| Wire Size mm²                 | 0.20-1.31                 |
| Electrical                    |                           |
| Current - Maximum per Contact | 8.0A                      |
| Voltage - Maximum             | 300V                      |
| Material Info                 |                           |
| Reference - Drawing Numbers   |                           |
| Product Specification         | PS-39500-001-001          |
| Sales Drawing                 | SD-39507-002              |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Relevant                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Relevant |
| ELV                                                           | Not Relevant |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

39507 Series

Mates With

Most 3.50mm Pitch Industry Standard PCB Headers, [39505](#) Vertical PCB Header with Threaded Retention Inserts, [39506](#) Horizontal PCB Header with Threaded Retention Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39507-2509