

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0423760428

Status:

Active

Description:

KK 100 Hdr Assy RA Bkwy 08 Ckt Tin

Documents:

Drawing (PDF)

Product Specification PS-10-07-001 (PDF)

Packaging Specification PK-40873-0041-001 (PDF)

Symbol Footprint Data SYM-22-28-6083-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

Application tooling part link

Application Tooling Part Link

11-20-1230

General

Product Family

Series

Product Name

UPC

PCB Headers

42376

KK 254

800753514799

Physical

Flammability

Net Weight

94V-0

0.563/g

Electrical

Voltage - Maximum

500V

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

Process Temperature max. C

005

WAVE

001

235

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

Symbol/Footprint Data

PK-40873-0041-001

PS-10-07-001

SD-42376-001-001, SD-42376-001-002

SYM-22-28-6083-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42376 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[42376-0428](#)