

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0511140410](#)  
**Status:** **Active**  
**Overview:** [Mighty-SPOX Connector System](#)  
**Description:** Mighty-SPOX Wire-to-Wire Plug Housing, 3.50mm Pitch, Positive Lock, with Optional Panel Mount, 4 Circuits

**Documents:**  
[3D Model](#)  
[3D Model \(PDF\)](#)  
[Drawing \(PDF\)](#)  
[Product Specification PS-51067-008 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**  
CSA LR19980  
UL E29179

**General**  
Product Family Crimp Housings  
Series [51114](#)  
Application Power  
Overview [Mighty-SPOX Connector System](#)  
Product Name Mighty-SPOX  
UPC 800754310086

**Physical**  
Circuits (maximum) 4  
Color - Resin Natural  
Flammability 94V-0  
Gender Plug  
Glow-Wire Capable No  
Material - Resin Polyester  
Net Weight 1582.000/mg  
Number of Rows 1  
Packaging Type Bag  
Panel Mount No  
Pitch - Mating Interface 3.50mm  
Stackable No  
Temperature Range - Operating -40° to +105°C

**Material Info**

**Reference - Drawing Numbers**  
Product Specification PS-51067-008  
Sales Drawing SD-51114-001



Series image - Reference only

**EU ELV**  
**Not Relevant**

**EU RoHS** **China RoHS**  
**Compliant**  
**REACH SVHC**  
Not Contained Per -  
ED/71/2019 (16 July  
2019)  
**Halogen-Free**  
**Status**  
**Not Low-Halogen**  
For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**  
[51114 Series](#)

**Mates With**  
[51067](#)

**Use With**  
[50419](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51114-0410](#)