

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638110000](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for 1.25mm Pitch Terminals on a Metal Strip, 26-32 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207129](#)
Comments <p>Hand tool 638110000 will process the 50058 series however to process the 50079 series you will also need to order die set 638113770 </p>. Type: 7

Function Crimp
Geographic Area Global
Level of Automation Manual
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name N/A
Tool Type Hand Crimp Tool
UPC 800754356916
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 0.001/g

Material Info

Reference - Drawing Numbers
Application Tooling Documents
ATS-638110000-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/30/2017 (7 July 2017) Halogen-Free Status Not Relevant For more information, please visit Contact US	China RoHS China ROHS Not Relevant ELV Not Relevant RoHS Phthalates Not Contained
---	---

Search Parts in this Series
[207129 Series](#)

Application Tooling Description	FAQ Product #
1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Reel	500588000
1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Reel	500798000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63811-0000](#)