

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638117200

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Sabre Terminals, 14-18 AWG



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

Field Repair, See Tooling Specification (PDF) Above.

Type: 4C

Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Hand Crimp Tool

800756681108

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

742.798/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-6381172HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
Sabre Crimp Terminal, Male, 18 AWG, 3.30mm Max. Insulation Diameter, Reel Packaged, Unplated, Brass Contact	431781001
Sabre Crimp Terminal, Male, 18 AWG, 3.30mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact	431781002
Sabre Crimp Terminal, Male, 18 AWG, 3.30mm Max.	431785002

Insulation Diameter,
Reel Packaged,
Tin (Sn) Plated
Brass Contact, Last-
Make Wipe Length,
complies with the
UL1977 finger proof
access requirement
Sabre Crimp 433740001
Terminal, Female,
14-16 AWG, 0.79mm
max. Insulation
Diameter, Reel
Packaged, Tin (Sn)
Plated Brass Contact
Sabre Single Crimp 433750001
Terminal, Female,
14-16 AWG, 3.30mm
Max. Insulation
Diameter, Reel
Packaged, Tin (Sn)
Plated Brass Contact
with TPA

This document was generated on 11/02/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63811-7200](#)