

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638138400

Status:


Active

Overview:

Application Tooling

Description:

Extractor Tool for MOX 0.635mm Receptacle Crimp Terminals



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207121
Comments	See Tooling Specification (PDF) Above
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	MOX
Tool Type	Extraction Hand Tool
UPC	884982141339
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Physical	
Net Weight	0.010/mg
Material Info	
Reference - Drawing Numbers	
Application Tooling Documents	ATS-638138400-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207121 Series

Use With

98982 2.54mm Pitch MOX Receptacle Kit, 4 Rows, 40 Circuits

Application Tooling Description	FAQ Product #
MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.60mm²), Reel, Tin (Sn)	986581211
MOX Crimp Terminal, Female, 0.635mm, 18-22 AWG (0.75mm²), Reel, Tin (Sn)	986581212
MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.50mm²), Reel, Tin (Sn)	986581213

MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.60mm²), Reel, Selective Gold	<u>986581221</u>
MOX Crimp Terminal, Female, 0.635mm, 18-22 AWG (0.75mm²), Reel, Selective Gold	<u>986581222</u>
MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.50mm²), Reel, Selective Gold	<u>986581223</u>
MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.60mm²), Reel, 2 Points Selective Gold	<u>986581231</u>
MOX Crimp Terminal, Female, 0.635mm, 18-22 AWG (0.75mm²), Reel, 2 Points Selective Gold	<u>986581232</u>
MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.50mm²), Reel, 2 Points Selective Gold	<u>986581233</u>
MOX MOUNTING HSG RCPT GRY 40CKT	<u>989820028</u>
2.54mm Pitch MOX Receptacle Kit, Dual Row, 20 Circuits, White	<u>989821010</u>
2.54mm Pitch MOX Receptacle Kit, Dual Row, 20 Circuits, Blue	<u>989821016</u>
2.54mm Pitch MOX Receptacle Kit, 4 Rows, 40 Circuits, White	<u>989821020</u>
2.54mm Pitch MOX Receptacle Kit, 4 Rows, 40 Circuits, Black	<u>989821021</u>
2.54mm Pitch MOX Receptacle Kit, 4 Rows, 40 Circuits, Blue	<u>989821026</u>
2.54mm Pitch MOX Receptacle Kit, 4 Rows, 40 Circuits, Gray	<u>989821028</u>

This document was generated on 11/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63813-8400](#)