

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638192300

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for iGrid Female Terminals, 22-26 AWG and 0.30-0.20mm² Wire



Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

See Tooling Specification (PDF) Above. Type: 4D Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Hand Crimp Tool

883906191245

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

317.100/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638192300-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit Contact US

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207129 Series

Use With

501647 2.00mm Pitch iGrid Wire-to-Board Crimp Terminal

Application Tooling Description	FAQ Product #
2.00mm Pitch, iGrid Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Reel	5016471000
2.00mm Pitch, iGrid Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Bag	5016471100
2.00mm Pitch, iGrid Female Crimp Terminal, 0.10µm Gold (Au) Plating, 22-24 AWG, Reel	5030952201

2.00mm Pitch, iGrid Female Crimp Terminal, 0.38µm Gold (Au) Plating, 22-24 AWG, Reel	<u>5030953201</u>
2.00mm Pitch, iGrid Female Crimp Terminal, 0.76µm Gold (Au) Plating, 22-24 AWG, Reel	<u>5030954201</u>

This document was generated on 11/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63819-2300