

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638194600

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for CLIK-Mate Wire-to Board Terminals, 24-28 AWG and 0.08 and 0.20mm² Wire

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

See Tooling Specification (PDF) Above. Type: 4A Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Hand Crimp Tool

883906422905

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

428.885/zg

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-6381946HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

502579 CLIK-Mate Wire-to-Board Crimp Terminal

Application Tooling Description	FAQ Product #
CLIK-Mate 1.50mm Pitch Wire-to-Board Male Crimp Terminal, 0.10µm Gold Plating, 24-26 AWG, Reel	2130281000
CLIK-Mate 1.50mm Pitch Wire-to-Board Male Crimp Terminal, 0.10µm Gold Plating, 24-26 AWG, Bag	2130281100
CLIK-Mate 1.50mm Pitch Wire-to-Board Male Crimp Terminal, 0.38µm	2130283000

Gold Plating, 24-26
AWG, Reel
CLIK-Mate 1.50mm [2130283100](#)
Pitch Wire-to-
Board Male Crimp
Terminal, 0.38µm
Gold Plating, 24-26
AWG, Bag
CLIK-Mate 1.50mm [2130287000](#)
Pitch Wire-to-
Board Male Crimp
Terminal, 0.76µm
Gold Plating, 24-26
AWG, Reel
CLIK-Mate 1.50mm [2130287100](#)
Pitch Wire-to-
Board Male Crimp
Terminal, 0.76µm
Gold Plating, 24-26
AWG, Bag
1.50mm Pitch, CLIK- [5025790000](#)
Mate Male Crimp
Terminal, Tin Plating,
24-28 AWG, Reel
1.50mm Pitch, CLIK- [5025790100](#)
Mate Male Crimp
Terminal, Tin Plating,
24-28 AWG, Bag

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63819-4600