

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638614100](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for C-Grid III Crimp Terminals, 22-24 AWG Wire with Insulation Diameter 1.00-1.60mm

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Application Tooling](#)
Series [207127](#)
Comments [See Tooling Specification \(PDF\) Above](#)
Function [Crimp](#)
Geographic Area [Global](#)
Level of Automation [Automatic, Semi-Automatic](#)
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name [FineAdjust](#)
Tool Type [Applicator](#)
UPC [800754852524](#)
Warranty Disclaimer [CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors \("Molex Tooling"\). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.](#)

Physical
Net Weight [5023.094/g](#)

Material Info

Reference - Drawing Numbers
[Application Tooling Documents](#)
[638614100-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001](#)



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
C-Grid III Crimp Terminal, 22-24 AWG, Reel, Tin (Sn)	901190109
C-Grid III Crimp Terminal, 22-24 AWG, Reel, 0.38µm Selective Gold (Au)	901190110
C-Grid III Crimp Terminal, 22-24 AWG, Reel, 0.76µm Selective Gold (Au)	901190111

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63861-4100