

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638834200

Status:

Active

Overview:

Application Tooling

Description:

Mini-Mac Applicator

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207127

Crimp

Global

Automatic, Semi-Automatic

applicationtooling@molex.com

Application Tooling

Mini-Mac

Applicator

822348746125

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

4846.632/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638834200-001, TM-638800000-001, TM-638800000SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Continuous Molded Strip, Tab 6.35 x 0.81mm, Blue	190030041
InsulKrimp Quick Disconnect, Female, Continuous Molded Strip, Tab 6.35 x 0.81mm	190030045
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Continuous Molded Strip, Tab 4.75 x 0.51mm, Blue	190030051
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Continuous Molded Strip, Tab 4.75 x 0.81mm, Aqua	190030057

	InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Continuous Molded Strip, Tab 5.21 x 0.51mm, Blue	<u>190030085</u>
	InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Continuous Molded Strip, Tab 5.21 x 0.81mm, Aqua	<u>190030086</u>
	InsulKrimp Quick Disconnect, Female, Continuous Molded Strip, Tab 4.75 x 0.51mm	<u>190030134</u>
	InsulKrimp Quick Disconnect, Female, Continuous Molded Strip, Tab 4.75 x 0.81mm	<u>190030137</u>
	Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Blue, 14-16 AWG, Continuous Strip	<u>192760004</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63883-4200](#)