

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638915100](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: [Mini-Mac Applicator](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Application Tooling](#)
Series [207127](#)
Comments [See Tooling Specification \(PDF\) Above](#)
Function [Crimp](#)
Geographic Area [Global](#)
Level of Automation [Automatic, Semi-Automatic](#)
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name [Mini-Mac](#)
Tool Type [Applicator](#)
UPC [800756656106](#)
Warranty Disclaimer [CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors \("Molex Tooling"\). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.](#)

Physical
Net Weight [4766.556/g](#)

Material Info

Reference - Drawing Numbers
[Application Tooling Documents](#) [ATS-638915100-001, TM-638000100-001, TM-638000100SP-001](#)

Series image - Reference only

EU ELV
Not Relevant

EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Relevant	China RoHS
---	-------------------

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207127 Series](#)

Use With
[Molex TM-3000: 638017200 , 638017300](#)
[, Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
KK High Pressure Crimp Terminal, Female, 24-30 AWG, Brass, 0.38µm Selective Gold (Au) Plating, Reel	8550124
KK High Pressure Crimp Terminal, Female, 24-30 AWG, Brass, 2.54µm Tin (Sn) Plating, Reel	50291900

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63891-5100](#)