

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638919100

Status:

Active

Overview:

Application Tooling

Description:

Mini-Mac Applicator, For Standard "B" Style Insulation Crimps

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207127

See Tooling Specification (PDF) Above

Crimp

Global

Automatic, Semi-Automatic

applicationtooling@molex.com

Application Tooling

Mini-Mac

Applicator

800756656175

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

4904.825/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638919100-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638000100-001, TM-638000100SP-001

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Relevant

Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Sabre Crimp Terminal, Male, Double 20 AWG, 4.57mm Max. Insulation Diameter, Reel Packaged, Unplated, Brass Contact	431782001
Sabre Crimp Terminal, Male, 14-16 AWG or double 18-20 AWG, 4.57mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact	431782002
Sabre Crimp Terminal, Male, 14-18 AWG, 4.57mm Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact, Last-Make Wipe Length, complies with the	431786002

This document was generated on 01/25/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63891-9100](#)