

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [0639018900](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** FineAdjust Applicator for Micro-Fit 3.0 Terminals, for 20-24 AWG Wire with Insulation Diameter 0.91-1.09mm

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**  
Product Family Application Tooling  
Series [207127](#)  
Comments See Tooling Specification (PDF) Above  
Function Crimp  
Geographic Area Global  
Level of Automation Automatic, Semi-Automatic  
More Detailed Tech Information [applicationtooling@molex.com](mailto:applicationtooling@molex.com)  
Overview [Application Tooling](#)  
Product Name FineAdjust  
Tool Type Applicator  
UPC 884982220577  
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**  
Net Weight 4977.245/g

**Material Info**

**Reference - Drawing Numbers**  
Application Tooling Documents  
ATS-639018900-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free Status</b><br><b>Not Relevant</b>             |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Relevant      |
| ELV                                                           | Not Relevant      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[207127](#) Series

**Use With**  
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

| Application Tooling Description                                                                             | FAQ Product #             |
|-------------------------------------------------------------------------------------------------------------|---------------------------|
| Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Reel         | <a href="#">430300001</a> |
| Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel | <a href="#">430300002</a> |
| Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au)                                                 | <a href="#">430300003</a> |

Plated Phosphor  
Bronze Contact,  
20-24 AWG, Reel  
Micro-Fit 3.0 Crimp [430310001](#)  
Terminal, Male,  
with Tin (Sn) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp [430310002](#)  
Terminal, Male,  
with 0.38µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp [430310003](#)  
Terminal, Male,  
with 0.76µm Select  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit TPA Crimp [430315003](#)  
Terminal, Male, with  
Tin (Sn) Pre-plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp [457730001](#)  
Terminal, Female,  
with Lubricant, with  
Tin (Sn) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp [457730003](#)  
Terminal, Female,  
with Lubricant, with  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel  
Micro-Fit 3.0 Crimp [457730053](#)  
Terminal, Female,  
with Lubricant, with  
Gold (Au) Plated  
Phosphor Bronze  
Contact, 20-24 AWG,  
Reel

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63901-8900](#)