

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640010200

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Insulkrimp Quick Disconnect Terminals, 10-22 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

ServiceGrade Hand Tool 640160037 Type RHT

Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Hand Crimp Tool

756054219881

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

RHT-1991

Reference - Drawing Numbers

Application Tooling Documents

ATS-640010200-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
Avikrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm²) Wire, Box, Tab 6.35 x 0.81mm	190020044
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Box, Tab 2.79 x 0.51mm	190170001
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire,	190170005

Box, Tab 2.79 x
0.81mm
InsulKrimp Quick 190170007
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 4.75 x
0.51mm
InsulKrimp Quick 190170008
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 4.75 x
0.81mm
InsulKrimp Quick 190170014
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 6.35 x
0.81mm
InsulKrimp Quick 190170018
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 5.21 x
0.51mm
InsulKrimp Quick 190170023
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 2.79 x
0.51mm
InsulKrimp Quick 190170028
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 2.79 x
0.81mm
InsulKrimp Quick 190170031
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 4.75 x
0.51mm
InsulKrimp Quick 190170032
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 4.75 x
0.81mm
InsulKrimp Quick 190170037
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 6.35 x
0.81mm
InsulKrimp Quick 190170043
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 5.21 x
0.51mm
InsulKrimp Quick 190170044
Disconnect,
Female, for 14-16

(2.00-1.30mm²) Wire,
Box, Tab 5.21 x
0.81mm
InsulKrimp Quick 190170047
Disconnect,
Female, for 10-12
(5.00-3.30mm²) Wire,
Box, Tab 6.35 x
0.81mm
Avikrimp Quick 190190001
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 2.79 x
0.51mm
Avikrimp Quick 190190004
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 2.79 x
0.81mm
Avikrimp Quick 190190006
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 4.75 x
0.51mm
Avikrimp Quick 190190008
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 4.75 x
0.81mm
Avikrimp Quick 190190012
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 6.35 x
0.81mm
Avikrimp Quick 190190014
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 5.21 x
0.51mm
Avikrimp Quick 190190015
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 5.21 x
0.81mm
Avikrimp Quick 190190022
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 2.79 x
0.51mm
Avikrimp Quick 190190025
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 2.79 x
0.81mm
Avikrimp Quick 190190027
Disconnect,

Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 4.75 x
0.51mm
Avikrimp Quick 190190028
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 4.75 x
0.81mm
Avikrimp Quick 190190031
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 6.35 x
0.81mm
Avikrimp Quick 190190034
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 5.21 x
0.51mm
Avikrimp Quick 190190035
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 5.21 x
0.81mm
Avikrimp Quick 190190037
Disconnect,
Female, for 10-12
(5.00-3.30mm²) Wire,
Box, Tab 6.35 x
0.81mm
Quixon Quick 192740002
Disconnect,
InsulKrimp Style,
Female, Partially
Insulated Red, 18-22
AWG, Loose
Quixon Quick 192740005
Disconnect,
InsulKrimp Style,
Female, Partially
Insulated Blue, 14-16
AWG, Loose
Quixon Quick 192750002
Disconnect, Avikrimp
Style, Female,
Partially Insulated
Red, 18-22 AWG,
Loose
Quixon Quick 192750005
Disconnect, Avikrimp
Style, Female,
Partially Insulated
Blue, 14-16 AWG,
Loose
Quixon Quick 192770008
Disconnect, Avikrimp
Style, Female, Fully
Insulated Yellow,
10-12 AWG, Loose
Avikrimp Fully 196060005
Insulated Quick

Disconnect, Female,
for 10-12 AWG Wire,
Box

This document was generated on 11/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64001-0200](#)