

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640050300

Status:

Active

Overview:

Application Tooling

Description:

Crimp Head for the AT-200 Pneumatic Hand Tool

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Air Tool
Tool Type	Pneumatic Hand Tool
UPC	756054563670
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

AT-1993

Reference - Drawing Numbers

Application Tooling Documents

640050300-001, ATS-640050300-001, TM-192790001-001, TM-192790001SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Molex AT-200 HandHeld Pneumatic Tool

192790001

Application Tooling Description	FAQ Product #
InsulKrimp Snap Plug, for 18-22 AWG Wire, 24.13mm Length	190340002
InsulKrimp Snap Plug, for 18-22 AWG Wire, 22.61mm Length	190340005
InsulKrimp Snap Plug, for 14-16 AWG Wire, 24.13mm Length	190340007
InsulKrimp Ring Tongue Terminal for 18-22 AWG Wire	190700005

InsulKrimp Ring	<u>190700007</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700009</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700011</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700013</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700015</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700021</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700023</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700026</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700033</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700038</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700040</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700044</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700051</u>
Tongue Terminal for	
18-22 AWG Wire	
InsulKrimp Ring	<u>190700059</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700063</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700065</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700067</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700069</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700071</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700073</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700075</u>
Tongue Terminal for	
14-16 AWG Wire	

InsulKrimp Ring	<u>190700078</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700083</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700086</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700090</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700099</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700102</u>
Tongue Terminal for	
14-16 AWG Wire	
InsulKrimp Ring	<u>190700109</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700115</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700119</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700121</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700123</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700130</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700132</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700136</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700143</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700145</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700150</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700153</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Ring	<u>190700155</u>
Tongue Terminal for	
10-12 AWG Wire	
InsulKrimp Snap	<u>190990007</u>
Spade Terminal for	
18-22 AWG Wire,	
Red	
InsulKrimp Snap	<u>190990009</u>
Spade Terminal for	
18-22 AWG Wire,	
Red	

	InsulKrimp Snap Spade Terminal for 18-22 AWG Wire, Red	<u>190990013</u>
	InsulKrimp Snap Spade Terminal for 18-22 AWG Wire, Red	<u>190990015</u>
	InsulKrimp Snap Spade Terminal for 14-16 AWG Wire, Blue	<u>190990025</u>
	InsulKrimp Snap Spade Terminal for 14-16 AWG Wire, Blue	<u>190990027</u>
	InsulKrimp Snap Spade Terminal for 14-16 AWG Wire, Blue	<u>190990032</u>
	InsulKrimp Snap Spade Terminal for 14-16 AWG Wire, Blue	<u>190990034</u>
	InsulKrimp Snap Spade Terminal for 10-12 AWG Wire, Yellow	<u>190990044</u>
	InsulKrimp Snap Spade Terminal for 10-12 AWG Wire, Yellow	<u>190990048</u>
	InsulKrimp Snap Spade Terminal for 10-12 AWG Wire, Yellow	<u>190990050</u>
	InsulKrimp Flanged Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5), Length 19.84mm	<u>191210005</u>
	InsulKrimp Flanged Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 8 (M4)	<u>191210007</u>
	InsulKrimp Flanged Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)	<u>191210009</u>
	InsulKrimp Flanged Spade Tongue Terminal for 14-16 AWG Wire, Stud Size 6 (M3.5)	<u>191210026</u>
	InsulKrimp Flanged Spade Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4)	<u>191210028</u>
	InsulKrimp Flanged Spade Tongue Terminal for 14-16	<u>191210030</u>

AWG Wire, Stud
Size 10 (M5), Length
20.19mm
InsulKrimp Flanged [191210046](#)
Spade Tongue
Terminal for 10-12
AWG Wire, Stud
Size 6 (M3.5), Width
8.13mm
InsulKrimp Flanged [191210047](#)
Spade Tongue
Terminal for 10-12
AWG Wire, Stud
Size 8 (M4), Width
8.13mm
InsulKrimp Flanged [191210049](#)
Spade Tongue
Terminal for 10-12
AWG Wire, Stud
Size 10 (M5), Width
8.13mm
InsulKrimp Flanged [191210051](#)
Spade Tongue
Terminal for 10-12
AWG Wire, Stud
Size 6 (M3.5), Width
9.53mm
InsulKrimp Flanged [191210053](#)
Spade Tongue
Terminal for 10-12
AWG Wire, Stud
Size 8 (M4), Width
9.53mm
InsulKrimp Block [191310002](#)
Spade Tongue
Terminal for 10 to
12 AWG Wire, Stud
Size 10 (M5), Length
27.31mm
InsulKrimp Block [191310004](#)
Spade Tongue
Terminal for 10 to
12 AWG Wire, Stud
Size 8 (M4), Length
27.31mm
InsulKrimp Block [191310006](#)
Spade Tongue
Terminal for 10
to 12 AWG Wire,
Stud Size 6 (M3.5),
Length 27.31mm
InsulKrimp Block [191310014](#)
Spade Tongue
Terminal for 14 to
16 AWG Wire, Stud
Size 10 (M5), Length
19.80mm
InsulKrimp Block [191310018](#)
Spade Tongue
Terminal for 14 to
16 AWG Wire, Stud
Size 8 (M4), Length
19.80mm
InsulKrimp Block [191310020](#)
Spade Tongue

	Terminal for 14 to 16 AWG Wire, Stud Size 6 (M3.5), Length 19.80mm InsulKrimp Block <u>191310023</u> Spade Tongue
	Terminal for 14 to 16 AWG Wire, Stud Size 6 (M3.5), Length 19.94mm InsulKrimp Block <u>191310025</u> Spade Tongue
	Terminal for 14 to 16 AWG Wire, Stud Size 4 (M2.6), Length 19.94mm InsulKrimp Block <u>191310031</u> Spade Tongue
	Terminal for 18 to 22 AWG Wire, Stud Size 6 (M3.5), Length 19.91mm InsulKrimp Block <u>191310034</u> Spade Tongue
	Terminal for 18 to 22 AWG Wire, Stud Size 10 (M5), Length 19.94mm InsulKrimp Block <u>191310036</u> Spade Tongue
	Terminal for 18 to 22 AWG Wire, Stud Size 8 (M4), Length 19.94mm InsulKrimp Block <u>191310038</u> Spade Tongue
	Terminal for 18 to 22 AWG Wire, Stud Size 6 (M3.5), Length 19.94mm InsulKrimp Block <u>191310042</u> Spade Tongue
	Terminal for 18 to 22 AWG Wire, Stud Size 6 (M3.5), Length 6.35mm InsulKrimp Block <u>191310045</u> Spade Tongue
	Terminal for 18 to 22 AWG Wire, Stud Size 4 (M2.6), Length 18.47mm InsulKrimp Block <u>191310047</u> Spade Tongue
	Terminal for 18 to 22 AWG Wire, Stud Size 2 (M2), Length 18.47mm InsulKrimp Spade <u>191440001</u> Tongue Terminal for
	18-22 AWG Wire InsulKrimp Spade <u>191440003</u> Tongue Terminal for 18-22 AWG Wire

InsulKrimp Spade Tongue Terminal for 18-22 AWG Wire	<u>191440005</u>
InsulKrimp Spade Tongue Terminal for 14-16 AWG Wire	<u>191440015</u>
InsulKrimp Spade Tongue Terminal for 14-16 AWG Wire	<u>191440018</u>
InsulKrimp Spade Tongue Terminal for 14-16 AWG Wire	<u>191440020</u>
InsulKrimp Spade Tongue Terminal for 14-16 AWG Wire	<u>191440024</u>
InsulKrimp Spade Tongue Terminal for 14-16 AWG Wire	<u>191440026</u>
InsulKrimp Spade Tongue Terminal for 10-12 AWG Wire	<u>191440037</u>
InsulKrimp Spade Tongue Terminal for 10-12 AWG Wire	<u>191440039</u>
InsulKrimp Spade Tongue Terminal for 10-12 AWG Wire	<u>191440042</u>
InsulKrimp Butt Splice for 18-22 AWG Wire	<u>191540004</u>
InsulKrimp Butt Splice for 18-22 AWG Wire	<u>191540011</u>
InsulKrimp Butt Splice for 14-16 AWG Wire	<u>191540015</u>
InsulKrimp Butt Splice for 14-16 AWG Wire	<u>191540023</u>
InsulKrimp Butt Splice for 10-12 AWG Wire	<u>191540028</u>
InsulKrimp Butt Splice for 10-12 AWG Wire	<u>191540037</u>
Perma-Seal Male Snap Plug for 18-22 AWG Wire, Diameter 3.96mm	<u>191640010</u>
Perma-Seal Male Snap Plug for 14-16 AWG Wire, Diameter 4.57mm	<u>191640039</u>
Perma-Seal Male Snap Plug for 14-16 AWG Wire, Diameter 3.96mm	<u>191640040</u>
Butt - Funnel Entry Splice for 14-16 AWG Wire	<u>192020019</u>
Funnel Entry Butt Splice for 14-16 AWG Wire	<u>192020027</u>

NylaKrimp Butt Splice for 14-16 AWG Wire	<u>192020031</u>
NylaKrimp Butt Splice for 10-12 AWG Wire	<u>192020049</u>
Funnel Entry Butt Splice for 18-22 AWG Wire	<u>192020063</u>
InsulKrimp 4 Way Splice for 18-22 AWG Wire	<u>192040003</u>
InsulKrimp 3 Way Splice for 18-22 AWG Wire	<u>192040004</u>
InsulKrimp 3 Way Splice for 14-16 AWG Wire	<u>192040014</u>
InsulKrimp 4 Way Splice for 10-12 AWG Wire	<u>192040025</u>
InsulKrimp 3 Way Splice for 10-12 AWG Wire	<u>192040026</u>
NylaKrimp Parallel Splice for 18-22 AWG Wire	<u>192070002</u>
NylaKrimp Parallel Splice for 14-16 AWG Wire	<u>192070004</u>
NylaKrimp Parallel Splice for 10-12 AWG Wire	<u>192070005</u>
InsulKrimp Wire Pin Terminal for 12-10 AWG Wire	<u>192120001</u>
InsulKrimp Wire Pin Terminal for 22-18 AWG Wire	<u>192120003</u>
InsulKrimp Wire Pin Terminal for 16-14 AWG Wire	<u>192120005</u>

This document was generated on 01/25/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64005-0300](#)