

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640050800

Status:

Active

Overview:

Application Tooling

Description:

Crimp Head for the AT-200 Pneumatic Hand Tool

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Air Tool
Tool Type	Pneumatic Hand Tool
UPC	756054591918
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

AT-5760

Reference - Drawing Numbers

Application Tooling Documents

ATS-640050800-001, TM-192790001-001, TM-192790001SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Molex AT-200 HandHeld Pneumatic Tool

192790001

Application Tooling Description	FAQ Product #
Avikrimp Fully Insulated Quick Disconnect, Female for 18-22 AWG Wire, Box	190020001
Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Box	190020005
Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Box	190020009

Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Box	<u>190020013</u>
Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Box	<u>190020016</u>
Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Box	<u>190020019</u>
Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Box	<u>190020021</u>
Quixon Quick Disconnect, Avikrimp Style, Female, Fully Insulated Red, 18-22 AWG, Loose	<u>192770002</u>

This document was generated on 11/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

64005-0800