

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0734151001

Status:

Active

Overview:

MMCX RF Connectors

Description:

50 Ohms, MMCX Right-Angle Jack, PCB, Gold (Au) Plated Body per Commercial Requirements, Tray

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

RF/Coax Connectors

Series

73415

Overview

MMCX RF Connectors

Product Name

MMCX

Style

PCB

Type

Microminiature

UPC

800755970708

Wire/Cable Type

N/A

Physical

Gender

Jack

Keying to Mating Part

None

Net Weight

0.436/g

Orientation

Right Angle

PCB Mounting

Through Hole

PCB Thickness - Recommended

2.40mm

Packaging Type

Tray

Panel Mount

No

Panel Mount Method

N/A

Reverse Polar

No

Electrical

Frequency

6 GHz

Impedance

50Ω

Power / Voltage

VOLTAGE: 170 Vrms@Sea Level

Solder Process Data

Duration at Max. Process Temperature (seconds)

010

Lead-freeProcess Capability

SMC&WAVE

Max. Cycles at Max. Process Temperature

002

Process Temperature max. C

260

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-73415-100-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73415 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73415-1001](#)