

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0747521301
Status: Active
Overview: SFP+ Passive Cable Assembly
Description: SFP+-to-SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 3.0m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E72548

General
Product Family Cable Assemblies
Series 74752
Assembly Configuration Dual Ended Connectors
Comments Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths., Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector SFP+-to-SFP+
Overview SFP+ Passive Cable Assembly
Product Name SFP Plus, SFP+
UPC 800756660851

Physical
Cable Length 3.0m
Circuits (Loaded) TWO DIFFERENTIAL PAIR
Gender Male-Male
Lock to Mating Part Yes
Material - Metal Beryllium Copper, Zinc Alloy
Net Weight 222.788/g
Packaging Type Bag
Single Ended No
Waterproof / Dustproof Yes
Wire Insulation Diameter N/A
Wire Size AWG 30
Wire/Cable Type Twinax

Electrical
Impedance 100Ω
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 3.3V

Material Info

Reference - Drawing Numbers
Sales Drawing 747520001-000



Series image - Reference only

EU ELV
Compliant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/61/2018 (27 June 2018) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV Green Image Compliant RoHS Phthalates Not Contained
---	---

Search Parts in this Series
74752 Series

Mates With
74441 SFP+ Host Connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74752-1301