

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0847320004

Status:

Active

Overview:

Sealed Industrial USB Solutions

Description:

Sealed Industrial USB Type A Plug-to-Sealed Industrial USB Type B Plug Double Ended Cord Set, 3.0m Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	84732
Assembly Configuration	Dual Ended Connectors
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-Pigtail
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	822348749355
Physical	
Cable Length	3.0m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Plug
Lock to Mating Part	None
Material - Resin	PVC
Net Weight	166.000/g
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Insulation Diameter	3.5mm (.14")
Wire Size AWG	N/A
Wire/Cable Type	USB
Electrical	
Current - Maximum per Contact	1.0A
Impedance	Non-constant
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)
Material Info	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

84732 Series

Mates With

84729 Sealed Industrial USB 2.0 Type A Panel Mount Receptacle to Sealed Industrial USB 2.0 Type A Plug Cordset. 847300001 SealedIndustrial USB 2.0 Type B Panel Mount PCB Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84732-0004](#)