

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0887328802](#)  
**Status:** **Active**  
**Overview:**  
**Description:** USB On-The-Go (OTG) Shielded I/O Cable Assembly, USB A-to-Mini B, USB 2.0, 1.80m Length, Black

**General**

Product Family	Cable Assemblies
Series	<a href="#">68768</a>
Assembly Configuration	Dual Ended Connectors
Connector to Connector	USB Type A-to-Mini-B
Overview	usb
Product Name	USB
UPC	800756208428

**Physical**

Cable Length	1.80m
Circuits (Loaded)	5
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	62.000/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	0.80mm, 2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	4.064µm
Single Ended	No
Termination Interface: Style	Through Hole
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Round

**Electrical**

Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	30V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-88740-012-001
Sales Drawing	SD-887328500-001

**EU ELV**  
**Compliant**

**EU RoHS**  
**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[68768](#) Series

**Mates With**

USB On-The-Go (OTG) Mini-B Receptacle  
[54819](#) , [48242](#) , [500075](#) , [67503](#). Universal  
Serial Bus Shielded Receptacle Type  
A [67329](#) , [67226](#) , [67230](#) , [89485](#).  
[54366](#) Universal Serial Bus Shielded I/O  
Receptacle

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[88732-8802](#)