

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936000244

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Stainless Steel Cable Gland with Gasket, for 20.00-25.00mm Cable, Pg29 Thread



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
Standard	DIN 40430
UPC	887191844565
Physical	
Cable Diameter	20.00-25.00mm
Flammability	UL 94V-0
Material - Cable Gland	Stainless Steel
Material - Gasket	Elastomer
Net Weight	133.000/g
Packaging Type	Bag
Panel Cutout Diameter	37.40mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg29
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68
Material Info	
Engineering Number	7000.7399.0

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Not Reviewed

Status

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93600 Series

Use With

Industrial connector, hoods, housings where higher protection and pulling strength are required, for sealed enclosures and boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0244](#)