

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010174

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Turned Crimp Contact for 16A Inserts and Modules, Female, Gold (Au)
Plated Copper Alloy, 0.50mm² (20 AWG), 100 per Bag



Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Contact Type		Turned Crimp
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Contacts
Product Name		GWconnect
UPC		887191874920
Physical		
Gender		Female
Material - Contact		Copper Alloy
Material - Plating		Gold
Net Weight		1.450/g
Number of Grooves		0
Packaging Type		Bag
Stripping Length		7.50mm
Wire Size AWG		20
Wire Size mm²		0.50
Electrical		
Current - Maximum per Contact		16.0A
Material Info		
Engineering Number		7300.6241.1

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93601 Series

Mates With

93601 Male Turned Crimp Contact

Use With

S-AC, S-EC, S-EE, S-EEE, S-EHV,S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0174](#)