

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936014710](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: Gwconnect STD - Standard S-CX/3A Shielded 50 Ohm Coaxial Connector, Male, 1-Pole, with Size 3A «21x21» Hood, with Gasket, Pg11/Pg13.5, Black

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Contact to be ordered Separately.
Component Size	3A «21x21»
Component Type	Coaxial Connector
IP Rating	IP66, IP67
Insert Series	S-CX
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect®
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
Type	STD
UPC	887191844442
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Hood Coating	Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Hood	Die-cast Aluminum
Material - Insert	Polycarbonate
Material - Peg	Die-cast Aluminum
Material - Shield/Shell	Zinc Alloy-Nickel Plated
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	1
Temperature Range - Operating	-40°C to +85°C
Thread Size	Pg11, Pg13.5
Thread Type	(Pg)
Wire Size AWG	26-12
Wire Size mm²	0.14-4.00
Electrical	
Current - Maximum per Contact	10.0A
Voltage	EN 61984: 50V 0.8kV 3
Material Info	
Engineering Number	7913.3514.0



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
Need more information on product environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93601](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-4710