

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936014732

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect RJ45 Wire Plug Assembly, Size 3A «21x21», Top Entry, 8p/4C Plug, Pg11 Metal Gland and Hood, with 2 Red Polarizing Keys, Grey



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Color - Cable Jacket	N/A
Component Size	3A «21x21»
Component Type	Wire Plug Assembly
IP Rating	IP66, IP67
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Modular Plugs / Jacks
Product Name	GWconnect
Type	RJ45
UPC	887191845883
Physical	
Entry Location	Top
Flammability	UL 94V-0
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Cable Gland	Stainless Steel
Material - Gasket	NBR
Material - Hood	Die-cast Aluminum
Material - Nut	Stainless Steel
Material - Plating	Gold
Material - Plug	PBT
Net Weight	60.000/g
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8p/4C
Temperature Range - Operating	-40° to +120°C
Thread Size	Pg11
Thread Type	(Pg)
Material Info	
Engineering Number	7940.3320.0

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-4732