

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936040115

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect Enclosure, Die-cast Aluminum, S-8100 Series, without External Mounting Flanges, 240 x 160 x 100mm Outside Dimensions, Grey RAL 7001

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93604</u>
IP Rating	IP66, IP69
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Die-cast Enclosures
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 62208, NEMA ICS5, NEMA250, NMX-J235/1-2
Type	STD
UPC	887191873909

Physical

Enclosure Coating	Polyester Powder
Enclosure Color	Grey RAL 7001
Internal Dimensions	232 x 151 x 93mm
Material - Enclosure	Die-cast Aluminum
Mounting Style	Internal Through Holes
Net Weight	1736.000/g
Outside Dimensions	240 x 160 x 100mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +125°C

Material Info

Engineering Number 8100.8021.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

93604 Series

Use With

DIN-rails, mounting supports, fixing screws,
metal plates, and ground terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93604-0115