

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936060157

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Patch Cord Cable Assembly, CAT5 (CAT5e) Plug-to-Plug, PROFINET Compliant, 8P4C Wiring, Fully Shielded, 2.0m

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93606
Color - Cable Jacket	Green
Comments	PROFINET Compliant, Class D up to 100 MHz acc. to ISO/IEC 11802
Component Type	Cable Assembly
IP Rating	IP20
Length	2.0m
Material - Outer Jacket	PUR
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Patch Cords
Product Name	GWconnect
Standard	EN 50173-1
Type	RJ45 CAT5
UPC	887191839615
Physical	
Cable Diameter	6.90mm
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Plating	Gold
Material - Plug	PBT
Net Weight	79.200/g
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8p/4C
Temperature Range - Operating	-20° to +70°C
Wire Size AWG	22
Material Info	
Engineering Number	2240.3245.2



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93606 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93606-0157](#)