

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200868674

Status:

Active

Overview:

Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable

Description:

Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 4 Poles, Female (90°) to Pigtail, 24 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120086
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	889056003797
Physical	
Cable Diameter	4.80mm (.189")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	111.000/g
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire Size AWG	24
Wire/Cable Type	UL 21215
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	404001B41M100
Reference - Drawing Numbers	
Sales Drawing	SD-120086-010-001



Series image - Reference only

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

Compliant with Exemption 3

Not Contained

Search Parts in this Series

120086 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200868674](#)