

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202530533

Status:

Active

Overview:

Contrinex Inductive and Photoelectric Sensors

Description:

Contrinex Inductive Sensor, M8 Fully Stainless Steel, 3mm Operating Distance, Embeddable, NPN, NO, 3-pin M8 Connector, 60mm Housing Length



Documents:

Product Specification 1202530533-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Sensors
Series	120253
IP Rating	IP68, IP69K
Overview	Contrinex Inductive and Photoelectric Sensors
Product Category	Inductive Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130069286
Physical	
Connection	Connector (M8, 3-pin)
Length	60mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel
Mounting Style	Embeddable
Net Weight	99.000/g
Operating Distance	3mm
Output	NO
Sensor Housing Size	M8
Temperature Range - Operating	-25° to +85°C
Electrical	
Polarity	NPN
Switching Frequency	≤ 1200 Hz
Material Info	
Engineering Number	DW-AS-701-M8-001
Reference - Drawing Numbers	
Product Specification	1202530533-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120253 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120253-0533](#)