

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202540018](#)
Status: **Active**
Overview: Contrinex Inductive and Photoelectric
Description: Contrinex Photoelectric Sensor, C12 (13.5 x 27.5mm) Housing, Background Suppression, 2 - 120mm Operating Distance, PNP, Light-ON, Potentiometer Sensitivity Adjustment, 2m 3-wire PVC Cable

Documents:

[Product Specification 1202540018-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Sensors
Series	120254
IP Rating	IP67
Operating Principle	Background Suppression
Overview	<u>Contrinex Inductive and Photoelectric</u>
Product Category	Photoelectric Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130066544

Physical

Connection	Cable (PVC 2m, 3-wire)
Housing Size	13.5 X 27.5mm
Material - Housing	ABS
Material - Window	PMMA
Operating Distance	2 - 120mm
Output	Light-ON
Sensor Housing Size	C12
Temperature Range - Operating	0° to +55°C

Electrical

Polarity	PNP
Switching Frequency	≤ 800 Hz

Material Info

Engineering Number	LHR-C12PA-PLK-303
--------------------	-------------------

Reference - Drawing Numbers

Product Specification	1202540018-000
-----------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[120254](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120254-0018](#)