

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300100494](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change A-Size Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 12.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
Series [130010](#)
Connector End A Mini-Change
Connector End B Mini-Change
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Mini-Change Connectors](#)
Product Name Mini-Change
Protocol DeviceNet
Region America
Type Double Ended
UPC 78678884068

Physical

Cable Diameter 10.41mm (.410")
Cable Length 12.0m (39.37")
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket TPE
Material - Connector Body TPE
Material - Coupling Nut Black Epoxy Coated Zinc
Material - Plating Mating Gold
Net Weight 1805.296/g
Orientation Straight to Straight
Poles 3
Temperature Range - Operating -20° to +105°C
Wire Size AWG 16
Wire/Cable Type TC-ER

Electrical

Current - Maximum per Contact 13.0A
Voltage - Maximum 600V

Material Info

Engineering Number 113030K13M120

Reference - Drawing Numbers

Sales Drawing SD-130010-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[130010](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

130010-0494