


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552400144](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar Control Cable, TPE Jacket, Unshielded, 12 Circuits, 1.00mm² with Green-Yellow Ground / 18 AWG with Green-Yellow Ground, 13.00mm (.512") Diameter, 1000.0m (3280.83') Length, Black

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	155240
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Signal and Control
UPC	889056455336
Physical	
Bending Radius - Minimum	> 10xOD
Cable Length	1000.0m
Circuits (Loaded)	12
Color - Cable Jacket	Black
Insulation	PVC
Material - Outer Jacket	TPE
Net Weight	0.010/g
Outer Jacket Diameter	13.00mm
Packaging Type	Wooden Drum
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	18
Wire Size mm ²	1.00
Wire/Cable Type	UL Listed PLTC
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V
Material Info	
Engineering Number	1X1000M



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[155240](#) Series

Use With
DIN Valve Connectors [121201](#) , [121202](#) , [121207](#) , [121208](#) , [121205](#) , [121211](#)
Micro-Change (M12) [120071](#)
Ultra-Lock (M12) [120085](#)
GWconnect Heavy Duty Connectors [93601](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155240-0144](#)