

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1553212006](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar Power Cable, WSOR Jacket, Braided Shielding Overall, 8 Circuits, 4x(2.50mm²) with Green-Yellow Ground + 2x(2x1.00mm² with Braided Shield) / 4x(14 AWG) with Green-Yellow Ground + 2x(2x18 AWG with Braided Shield), 14.10mm (.555") Diameter, 1000.0m (3280.83') Length, Orange

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	155321
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Servo Motor
UPC	889056460927
Physical	
Bending Radius - Minimum	> 10xOD
Cable Length	1000.0m
Circuits (Loaded)	8 (4+2+2)
Color - Cable Jacket	Orange
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.010/g
Outer Jacket Diameter	14.10mm
Packaging Type	Wooden Drum
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	14, 18
Wire Size mm ²	1.00, 2.50
Wire/Cable Type	UL AWM 21939 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	1000V
Material Info	
Engineering Number	1X1000M



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[155321](#) Series

Use With
Brad M23 [120230](#) , [120233](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155321-2006](#)