


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1554111005](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar PROFIBUS* DP Network Cable, PVC Jacket, Braided Shielding Overall, 2 Circuits, 0.34mm² / 22 AWG, 8.20mm (.323") Diameter, 500.0m (1640.42') Length, Violet

Documents:
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	155411
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Network
Protocol	PROFIBUS
UPC	889056462617
Physical	
Bending Radius - Minimum	> 15xOD
Cable Length	500.0m
Circuits (Loaded)	2
Color - Cable Jacket	Violet
Insulation	Foam PE
Material - Outer Jacket	PVC
Net Weight	0.010/g
Outer Jacket Diameter	8.20mm
Packaging Type	Reel
Temperature Range - Operating	+5° to +60°C
Wire Size AWG	22
Wire Size mm ²	0.34
Wire/Cable Type	UL AWM 2464 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V
Material Info	
Engineering Number	1X500M



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[155411](#) Series

Use With

Brad M23 [120230](#) , [120233](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155411-1005](#)