

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1728900710](#)
Status: **Active**
Overview: [MediSpec Product Family](#)
Description: MPC Male Plug, Disposable, Key AA, 7 Circuits

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	I/O Connectors
Series	172890
Application	Wire-to-Wire
Component Type	Plug
Overview	MediSpec Product Family
Product Name	MPC
Type	N/A
UPC	889056271189
Physical	
Circuits (Loaded)	7
Circuits (maximum)	17
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Male
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polycarbonate
Net Weight	4.008/g
Orientation	Straight
Packaging Type	Embossed Tape on Reel
Panel Mount	N/A
Pitch - Mating Interface	N/A
Plating min - Mating	0.127µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Solder Cup
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP50
Electrical	
Current - Maximum per Contact	1.6A
Voltage - Maximum	300V AC (RMS)
Material Info	
Engineering Number	1728900710-FCT
Reference - Drawing Numbers	
Sales Drawing	SD-172890-0710



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per -ED/88/2018 (15 January 2019) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[172890 Series](#)

Mates With
MPC Female Receptacle [1723500710](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[172890-0710](#)