

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2035581307

Status:

Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Right-Angle, Surface Mount, 0.38µm Gold Plated, Inner Positive Lock, 13 Circuits, Natural

Documents:	
3D Model	Product Specification 5013301000-PS-CHI-002 (PDF)
Drawing (PDF)	Product Specification 5013301000-PS-JAP-002 (PDF)
3D Model (PDF)	Application Specification 5013300000-AS-000 (PDF)
Product Specification 5013300000-PS-002 (PDF)	Packaging Specification 2035589200-200 (PDF)
Product Specification 5013301000-PS-002 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	203558
Application	Signal, Wire-to-Board
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
UPC	191128156516

Physical	
Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	187.470/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.380µm
Plating min - Termination	0.051µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	100V AC (RMS)/DC

Material Info



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
203558 Series

Mates With
Pico-Clasp Female Housing 501330

Reference - Drawing Numbers

Application Specification	5013300000-AS-000
Packaging Specification	2035589200-200
Product Specification	5013300000-PS-002, 5013301000-PS-002, 5013301000-PS-CHI-002, 5013301000-PS-JAP-002
Sales Drawing	2035580000-SD-000

This document was generated on 02/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[203558-1307](#)