

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936000042

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Metal Cable Gland, with Washer and Gaskets, Pg21 Thread



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 10.00, 13.00, 16.00, and 19.00mm internal diameters.
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
UPC	887191826141
Physical	
Cable Diameter	9.50-18.50mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	35.000/g
Packaging Type	Bag
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg21
Thread Type	(Pg)
Material Info	
Engineering Number	7000.6844.0

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

93600 Series

Use With

Enclosures Size A and B metal type

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0042](#)