

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010422](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Turned Crimp Contact for 40A Inserts and Modules, Male, Silver \(Ag\)](#)
[Plated Copper Alloy, 6.00mm² \(10 AWG\), 100 per Bag](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 936010406-S00 \(PDF\)](#)

Agency Certification

CSA 256883
UL E249674

General

Product Family Industrial Connectors / Enclosures
Series [93601](#)
Contact Type Turned Crimp
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
Product Category Contacts
Product Name GWconnect
UPC 887191889306

Physical

Gender Male
Material - Contact Copper Alloy
Material - Plating Silver
Net Weight 3.400/g
Number of Grooves 0
Packaging Type Bag
Stripping Length 9.60mm
Wire Size AWG 10
Wire Size mm² 6.00

Electrical

Current - Maximum per Contact 40.0A

Material Info

Engineering Number 7600.5713.0

Reference - Drawing Numbers

Product Specification 936010406-S00
Sales Drawing 936010422-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS 50 Image
ELV Not Reviewed
RoHS Phthalates Not Contained

Search Parts in this Series

[93601](#) Series

Mates With

[93601](#) Female Turned Crimp Contact

Use With

S-K, S-Q, S-QD, and S-M Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0422