

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936014832](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect RJ45 Wire Plug Assembly, Size 3A «21x21», Side Entry, 8p/8C + 2pC Plug, M20 Metal Gland and Hood, with 2 Red Polarizing Keys, Grey



Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Color - Cable Jacket	N/A
Component Size	3A «21x21»
Component Type	Wire Plug Assembly
IP Rating	IP66, IP67
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Modular Plugs / Jacks
Product Name	GWconnect®
Type	RJ45
UPC	887191852904

Physical	
Entry Location	Side
Flammability	UL 94V-0
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Cable Gland	Stainless Steel
Material - Gasket	NBR
Material - Hood	Die-cast Aluminum
Material - Nut	Stainless Steel
Material - Plating	Gold
Material - Plug	PBT
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8p/8C + 2pC
Temperature Range - Operating	-40°C to +120°C
Thread Size	M20
Thread Type	(M) Metric

Material Info	
Engineering Number	7982.3422.0

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

REACH SVHC
Not Reviewed

Halogen-Free
Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93601](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-4832](#)