

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936060219
Status: Active
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect Patch Cord Cable Assembly, CAT5 (CAT5e) Plug-to-Plug, 8P4C Wiring, Fully Shielded, Size 3A «21x21» , STD - Standard Plastic Hood, Top Entry, M20 Plastic Gland, 1.0m

Documents:
RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93606
Boot	No
Cable Gland Type	IP66 - Basic
Color - Cable Jacket	Grey
Comments	Class D up to 100 MHz acc. to ISO/IEC 11802
Component Size	3A «21x21»
Component Type	Cable Assembly
IP Rating	IP66, IP67
Length	1.0m
Material - Outer Jacket	PVC
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Patch Cords
Product Name	GWconnect
Standard	EN 50173-1
Type	RJ45 CAT5
UPC	887191843766

Physical	
Cable Diameter	6.90mm
Gender	Plug/Plug
Gland Color	Black RAL 9005
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Hood	Polyamide
Material - Nut	Polyamide
Material - Plating	Gold
Material - Plug	PBT
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8p/4C
Temperature Range - Operating	-20°C to +70°C
Wire Size AWG	24

Material Info	
Engineering Number	2440.3244.1



Series image - Reference only

EU ELV
Not Reviewed
EU RoHS
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93606 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93606-0219](#)