

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936060322](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Patch Cord Cable Assembly, CAT5 (CAT5e) Plug-to-Plug, 8P/4C + 2PC Wiring, Fully Shielded, Size 3A «21x21» , HE - Harsh Environment Black Metal Hood, Top Entry, M20 Metal Gland, 1.50m

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Industrial Connectors / Enclosures
Series [93606](#)
Boot No
Cable Gland Type IP66 - Basic
Color - Cable Jacket Green
Comments Class D up to 100 MHz acc. to ISO/IEC 11802
Component Size 3A «21x21»
Component Type Cable Assembly
IP Rating IP66, IP67
Length 1.50m
Material - Outer Jacket PUR
Overview [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Product Category Patch Cords
Product Name GWconnect
Standard EN 50173-1
Type RJ45 CAT5
UPC 887191850801

Physical
Cable Diameter 6.80mm
Entry Location Top
Gender Plug/Plug
Hood Coating Polyester Powder
Hood Color Black RAL 9005
Lock to Mating Part Yes
Material - Cable Gland Metal
Material - Hood Die-cast Aluminum
Material - Nut Metal
Material - Plating Gold
Material - Plug PBT
Packaging Type Bag
Polarized to Mating Part Yes
Poles 8p/4C + 2pC
Temperature Range - Operating -20°C to +70°C
Thread Size M20
Thread Type (M) Metric
Wire Size AWG 22, 26

Material Info
Engineering Number 2642.3246.B

EU ELV
Not Reviewed
EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93606 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93606-0322](#)