

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1062841025

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

CXP Optical Cable Assembly (iPass+), MTP-to-MTP, Multimode, 50/125µm, Round Cable Assembly, Straight Boot, High Bandwidth, OFNP, Cable Diameter 5.40mm, Cable Length 25.00m

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Fiber Optic Assemblies
Series	106284
Boot Type	Straight
Connector to Connector	MTP-to-MTP
Mode	Multimode
Overview	Optical Connectivity Solutions
Product Name	CXP, iPass+, MTP
UPC	883906550219
Physical	
Cable Length	25.0m
Cable Size	3.80mm
Fiber (Core/Cladding)	50/125µm
Net Weight	411.500/g
Single Ended	No
Wire/Cable Type	Fiber Optic, Round
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-106284-0001-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
106284 Series
Mates With
CXP Optical Transceivers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106284-1025](#)