

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202530258](#)
Status: **Active**
Overview: [Contrinex Inductive and Photoelectric](#)
Description: Contrinex Inductive Sensor, M30 Housing, 10mm Operating Distance, Embeddable, NPN, NO, 4-pin M12 Connector, 63.5mm Housing Length

Documents:

[Product Specification 1202530258-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Sensors
Series	120253
IP Rating	IP67
Overview	Contrinex Inductive and Photoelectric
Product Category	Inductive Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130064359

Physical

Connection	Connector (M12, 4-pin)
Length	63.5mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Embeddable
Operating Distance	10mm
Output	NO
Sensor Housing Size	M30
Temperature Range - Operating	-25° to +70°C

Electrical

Polarity	NPN
Switching Frequency	≤ 1200 Hz

Material Info

Engineering Number	DW-AS-601-M30-002
--------------------	-------------------

Reference - Drawing Numbers

Product Specification	1202530258-000
-----------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120253](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120253-0258](#)