

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202530557

Status:

Active

Overview:

Contrinex Inductive and Photoelectric Sensors

Description:

Contrinex Inductive Sensor, M12 Fully Stainless Steel, 3mm Operating Distance, Embeddable, NPN, NO, 4-pin M12 Connector, 60mm Housing Length

Documents:

Product Specification 1202530557-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Sensors
Series	120253
IP Rating	IP68, IP69K
Overview	Contrinex Inductive and Photoelectric Sensors
Product Category	Inductive Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130069828
Physical	
Connection	Connector (M12, 4-pin)
Length	60mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel
Mounting Style	Embeddable
Net Weight	444.000/g
Operating Distance	6mm
Output	NO
Sensor Housing Size	M12
Temperature Range - Operating	-25° to +85°C
Electrical	
Polarity	NPN
Switching Frequency	≤ 600 Hz
Material Info	
Engineering Number	DW-AS-701-M12
Reference - Drawing Numbers	
Product Specification	1202530557-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120253 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120253-0557