

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202540126

Status:

Active

Overview:

Contrinex Inductive and Photoelectric Sensors

Description:

Contrinex Photoelectric Sensor, M18 Plastic Housing, Reflex, 20 - 7000mm Operating Distance, PNP, Changeover/IOL, 4-pin M12 Connector, 37mm Housing Length



Documents:

Product Specification 1202540126-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Sensors
Series	120254
IP Rating	IP67
Operating Principle	Reflex
Overview	Contrinex Inductive and Photoelectric Sensors
Product Category	Photoelectric Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130068722
Physical	
Connection	Connector (M12, 4-pin)
Length	37mm
Material - Housing	ABS
Material - Window	PMMA
Net Weight	152.000/g
Operating Distance	20 - 7000mm
Output	Changeover/IOL
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C
Electrical	
Polarity	PNP
Switching Frequency	≤ 1500 Hz
Material Info	
Engineering Number	LRR-M18PA-NMS-603
Reference - Drawing Numbers	
Product Specification	1202540126-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120254 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[120254-0126](#)