

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300060386](#)
Status: **Active**
Overview:
Description: Mini-Change A-Size Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 16 AWG, Rubber Cable, 9.14m (30.0') Length

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
Series [130006](#)
Connector End A Mini-Change
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview minichange_products
Product Name Mini-Change
Protocol N/A
Region America
Type Single Ended
UPC 78678844364

Physical

Cable Diameter 10.67mm (.420")
Cable Length 9.14m (30.0')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket Rubber
Material - Connector Body PVC
Material - Coupling Nut Black Epoxy Coated Zinc
Material - Plating Mating Gold
Net Weight 3666.000/g
Orientation Straight to Pigtail
Poles 3
Temperature Range - Operating -20° to +90°C
Wire Size AWG 16
Wire/Cable Type SOO

Electrical

Current - Maximum per Contact 13.0A
Voltage - Maximum 600V

Material Info

Engineering Number 103000C01F300

Reference - Drawing Numbers

Sales Drawing SD-130006-023-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

Search Parts in this Series

[130006](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300060386