



0.30MM CENTER FFC JUMPER CABLE CHART


"A" DIM.	2 ± .08 INCHES 51 ± 2 MM	4 ± .16 INCHES 102 ± 4 MM	6 ± .16 INCHES 152 ± 4 MM	8 ± .20 INCHES 203 ± 5 MM	10 ± .20 INCHES 254 ± 5 MM	12 ± .20 INCHES 305 ± 5 MM
CKTS: 9	150320209	150320409	150320609	150320809	150321009	150321209
CKTS: 11	150320211	150320411	150320611	150320811	150321011	150321211
CKTS: 13	150320213	150320413	150320613	150320813	150321013	150321213
CKTS: 15	150320215	150320415	150320615	150320815	150321015	150321215
CKTS: 17	150320217	150320417	150320617	150320817	150321017	150321217
CKTS: 19	150320219	150320419	150320619	150320819	150321019	150321219
CKTS: 21	150320221	150320421	150320621	150320821	150321021	150321221
CKTS: 23	150320223	150320423	150320623	150320823	150321023	150321223
CKTS: 25	150320225	150320425	150320625	150320825	150321025	150321225
CKTS: 27	150320227	150320427	150320627	150320827	150321027	150321227
CKTS: 31	150320231	150320431	150320631	150320831	150321031	150321231
CKTS: 33	150320233	150320433	150320633	150320833	150321033	150321233
CKTS: 35	150320235	150320435	150320635	150320835	150321035	150321235
CKTS: 37	150320237	150320437	150320637	150320837	150321037	150321237
CKTS: 39	150320239	150320439	150320639	150320839	150321039	150321239
CKTS: 41	150320241	150320441	150320641	150320841	150321041	150321241
CKTS: 43	150320243	150320443	150320643	150320843	150321043	150321243
CKTS: 45	150320245	150320445	150320645	150320845	150321045	150321245
CKTS: 51	150320251	150320451	150320651	150320851	150321051	150321251



NOTES:

1. SUBSTRATE AND COVERLAY MATERIAL IS .001" [25uM] POLYIMIDE.
2. CONDUCTOR IS 1/2 OZ (.0007") [18um] COPPER.
3. PLATING IS 2 MICRO INCHES MINIMUM OF HARD GOLD OVER 100 MICRO INCHES MINIMUM OF NICKEL.
4. TAIL ENDS ARE .008±.001 [0.20±0.03] THICK.
5. JUMPER CABLES ARE SUITABLE FOR USE WITH MOLEX 503566 SERIES CONNECTOR.



FUNCTIONAL SYMBOLS  = 0  = 0  = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	DIMENSION UNITS		SCALE		CURRENT REV DESC: PRODUCTION RELEASE			 .3MM PITCH JUMPER CABLES		
	MM/INCH		4:1							
	GENERAL TOLERANCES (UNLESS SPECIFIED)									
DIVISIONAL SYMBOLS			mm		INCH	EC NO: 701160				
	4 PLACES	±----		±----		DRWN: MIMIG	2022/03/28			
	3 PLACES	±----		±0.01		CHK'D: JSMITH11	2022/03/30			
	2 PLACES	±----		±0.03		APPR: JSMITH11	2022/03/30			
	1 PLACE	±----		±----		INITIAL REVISION:				
	0 PLACES	±----		±----		DRWN: MIMIG	2022/03/28			
ANGULAR TOL ± 1.0 °					APPR: JSMITH11		2022/03/30			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
						C-SIZE	15032	SEE CHART	GENERAL MARKET	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[15032-0209](#) [15032-0211](#) [15032-0213](#) [15032-0215](#) [15032-0217](#) [15032-0219](#) [15032-0221](#) [15032-0223](#) [15032-0225](#) [15032-0227](#) [15032-0231](#) [15032-0233](#) [15032-0235](#) [15032-0237](#) [15032-0239](#) [15032-0241](#) [15032-0243](#) [15032-0245](#) [15032-0251](#) [15032-0409](#) [15032-0411](#) [15032-0413](#) [15032-0415](#) [15032-0417](#) [15032-0419](#) [15032-0421](#) [15032-0423](#) [15032-0425](#) [15032-0427](#) [15032-0431](#) [15032-0433](#) [15032-0435](#) [15032-0437](#) [15032-0439](#) [15032-0441](#) [15032-0443](#) [15032-0445](#) [15032-0451](#) [15032-0609](#) [15032-0611](#) [15032-0613](#) [15032-0615](#) [15032-0617](#) [15032-0619](#) [15032-0621](#) [15032-0623](#) [15032-0625](#) [15032-0627](#) [15032-0631](#) [15032-0633](#) [15032-0635](#) [15032-0637](#) [15032-0639](#) [15032-0641](#) [15032-0643](#) [15032-0645](#) [15032-0651](#) [15032-0809](#) [15032-0811](#) [15032-0813](#) [15032-0815](#) [15032-0817](#) [15032-0819](#) [15032-0821](#) [15032-0823](#) [15032-0825](#) [15032-0827](#) [15032-0831](#) [15032-0833](#) [15032-0835](#) [15032-0837](#) [15032-0839](#) [15032-0841](#) [15032-0843](#) [15032-0845](#) [15032-0851](#) [15032-1009](#) [15032-1011](#) [15032-1013](#) [15032-1015](#) [15032-1017](#) [15032-1019](#) [15032-1021](#) [15032-1023](#) [15032-1025](#) [15032-1027](#) [15032-1031](#) [15032-1033](#) [15032-1035](#) [15032-1037](#) [15032-1039](#) [15032-1041](#) [15032-1043](#) [15032-1045](#) [15032-1051](#)