


**NOTES**

Signal: 32 AWG, Solid Silver Plated Copper

Insulation: FEP, 0.023" +/- 0.001"

Color: One Blue, One Green

Shield: Aluminum/Polyester Tape Wrap (Aluminum Side Out)

Braid Shield: 44 AWG Tin Plated Copper, >90% Coverage

Jacket: Polyurethane, 0.006" Wall Thickness, Black

Differential Impedance: 100 +/- 5 Ohms

Capacitance: 14.5 pF/ft Ref.

Propagation Delay: 1.45 +/- 0.01 ns/ft

Within Pair Skew: 5ps/ft Max.

This document is the
property of TEMP-FLEX.
It may not be disclosed,
reproduced, or otherwise
used without permission.

Rev

DCR

Description

App'd

Date

A

5888

Updated PN from 1000680065 to 1000560065.

KP

3/28/22

B

5897

Updated Prop Delay.

KP

6/3/22

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[100056-0065](#)